



AD925J

**RCBO 1P+N 6kA B-25A 30mA A Class**

**Technical properties**

**Architecture**

Type of pole	1P+N
Curve	B

**Electric current**

Rated current	25 A
Rated residual operating current I <sub>Δn</sub>	30 mA
Rated current -25°C	28.20 A
Rated current at -20°C	27.90 A
Rated current -15°C	27.60 A
Rated current -10°C	27.40 A
Rated current -5°C	27.10 A
Rated current at 0°C	26.80 A
Rated current 5°C	26.50 A
Rated current 10°C	26.20 A
Rated current 15°C	25.90 A
Rated current at 20°C	25.60 A
Rated current 25°C	25.30 A
Rated current 30°C	25 A
Rated current 35°C	24.80 A
Rated current at 40°C	24.50 A
Rated current at 50°C	24 A
Rated current 55°C	23.80 A
Rated current 60°C	23.50 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP2X

**Main electrical attributes**

### Connectivity

Type of connection	Screw terminal
--------------------	----------------

### Voltage

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4,000 V
Max. operating voltage	240 V
Rated operational voltage U <sub>e</sub>	240 - 240 V
Overvoltage category according to IEC 60947-1	3

### Power

Total power loss under I <sub>N</sub>	9.30 W
---------------------------------------	--------

### Frequency

Frequency	50 - 50 Hz
-----------	------------

### Use conditions

Max. Altitude	2,000 m
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

### Endurance

Electric endurance in number of cycles	2,000
Number of mechanical operations	2,000

### Connection

Cross-section flexible conductor	1 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

### Installation, mounting

Nominal tightening torque	2.10 - 2.10 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

### Capacity

Number of modules	2
-------------------	---

### Dimensions

Height	83 mm
--------	-------

---

Width	35 mm
Depth	68 mm