



CEA580W

RCCB 1P+N 80A 100mA A

Technical properties

Architecture

Type of pole	1P+N
--------------	------

Electric current

Rated current	80 A
Rated residual operating current I_{dn}	100 mA
Breaking and opening capacity I_{dm}	1.25 kA
Rated conditional short-circuit current I_{nc} according to EN61008-1	10 kA
Rated current -25°C	80 A
Rated current at -20°C	80 A
Rated current -15°C	80 A
Rated current -10°C	80 A
Rated current -5°C	80 A
Rated current at 0°C	80 A
Rated current 5°C	80 A
Rated current 10°C	80 A
Rated current 15°C	80 A
Rated current at 20°C	80 A
Rated current 25°C	80 A
Rated current 30°C	80 A
Rated current 35°C	80 A
Rated current at 40°C	80 A
Rated current at 45°C	80 A
Rated current at 50°C	80 A
Rated current 55°C	80 A
Rated current 60°C	80 A
Rated current 65°C	80 A
Rated current 70°C	75 A

Installation, mounting

Nominal tightening torque top terminal	3.60 - 3.60 Nm
Nominal tightening torque down terminal	3.60 - 3.60 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

Voltage

Rated operational voltage U_e	230 - 230 V
---------------------------------	-------------

Type voltage supply	AC
Rated insulation voltage Ui	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage Uimp	4,000 V
Rated impulse withstand voltage Uimp IEC 60947-3	6,000 V
Max. operating voltage	253 V
Frequency	
Frequency	50 - 60 Hz
Capacity	
Number of modules	2
Compatibility	
Suitable for DIN Rail	Yes
Safety	
Residual current type	A
Ingress Protection (IP) class	IP20
Connection	
Cross-section of output with screws, for massive conductors	1 - 50 mm ²
Cross-section of output with screws, for flexible conductors	1 - 35 mm ²
Power	
Total power loss under IN	10.90 W
Use conditions	
Max. Altitude	2,000 m
Operating temperature	-25 - 65 °C
Endurance	
Electric endurance in number of cycles	10,000
Number of mechanical operations	20,000
Connectivity	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Dimensions	
Height	85 mm
Width	36 mm
Depth	70 mm