




HAB402



Load break switch 4P 20A

Technical properties

Electric current

Rated current	20 A
Acceptable current rating AC21	20 A
Acceptable current rating AC21 category B	20 A
Acceptable current rating AC22 category B	20 A
Acceptable current rating AC23 category A	20 A
Acceptable current rating AC23 category B	20 A
Rated short-circuit making capacity I_{cm} under 415 V AC according to IEC 60947-3	1.80 kA
Rated short-time withstand current I_{cw} 1s IEC 60947	1.26 kA
Rated short-time withstand current I_{cw} IEC 60947	1.26 kA

Architecture

Type of pole	4P
Control/operation element	Short rotary handle
Number of poles	4

Connection

Cross-section rigid conductor	16 mm ²
-------------------------------	--------------------

Voltage

Rated insulation voltage U_i	800 V
Rated impulse withstand voltage U_{imp}	8,000 V
Rated operational voltage U_e	380 - 415 V

Power

Power loss per pole at I_n	0.30 W
Total power loss under I_N	1 W
Rated operational power under 400 V AC AC1	13,000 W
Rated operational power under 400 V AC AC23	9,000 W

Installation, mounting

Nominal tightening torque	2 - 2.2 Nm
---------------------------	------------

Equipment

Motor drive optional	No
Number of auxiliary contacts as change- over contact	0

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Use conditions	
Operating temperature	-20 - 70 °C
Cover, door	
Interlockable	Yes
Safety	
Ingress Protection (IP) class	IP20
Frequency	
Frequency	50 - 50 Hz
Connectivity	
Type of connection	Screw terminal
Functions	
Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes
Capacity	
Number of modules	3.42