



HDA033L

**Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 32A 18kA CTC**

**Technical properties**

**Electric current**

Rated current	32 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	18 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	42 A
Rated current 15°C according to IEC 60947	40.90 A
Rated current 20°C according to IEC 60947	39.80 A
Rated current 25°C according to IEC 60947	38.60 A
Rated current 30°C according to IEC 60947	37.30 A
Rated current at 35°C according to IEC 60947	36.10 A
Rated current at 40°C according to IEC 60947	34.70 A
Rated current 45°C according to IEC 60947	33.40 A
Rated current 50°C according to IEC 60947	32 A
Rated current 55°C according to IEC 60947	30.50 A
Rated current 5°C according to IEC 60947	40.90 A
Rated current at 60°C according to IEC 60947	28.90 A
Rated current 65°C according to IEC 60947	27.20 A
Rated current 70°C according to IEC 60947	25.40 A

**Architecture**

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8,000 V
Rated insulation voltage Ui	690 V

<b>Functions</b>	
Trip unit	TM F/F
<b>Power</b>	
Total power loss under IN	8.40 W
<b>Endurance</b>	
Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000
<b>Safety</b>	
Ingress Protection (IP) class	IP4X
<b>Connection</b>	
Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>
<b>Connectivity</b>	
Type of connection	Screw terminal
<b>Settings</b>	
Thermal protection knob setting xIN	1, 1
<b>Dimensions</b>	
Height	130 mm
Width	100 mm
Depth	68 mm
<b>Compatibility</b>	
Suitable for DIN Rail	Yes
<b>Installation, mounting</b>	
Mounting-/Connection Position	Front
<b>Main electrical attributes</b>	
Magnetic protection trip time	0 - 0 ms