



HMD190



## MCB 1P 15kA D-100A 1.5M

### Technical properties

#### Architecture

Type of pole	1P
Curve	D

#### Voltage

Rated operational voltage Ue	240 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6,000 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Installation, mounting

Nominal tightening torque	3.5 - 5.0 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

#### Electric current

Rated current	100 A
Rated service breaking capacity Ics AC according to IEC 60898-1	7.50 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	15 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	15 kA
Rated current at 0°C	124 A
Rated current 5°C	120 A
Rated current 10°C	116 A
Rated current 15°C	112 A
Rated current at 20°C	108 A
Rated current 25°C	104 A
Rated current 30°C	100 A
Rated current 35°C	96.60 A
Rated current at 40°C	93.10 A
Rated current at 45°C	89.40 A
Rated current at 50°C	85.60 A
Rated current 55°C	81.60 A
Rated current 60°C	77.50 A

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	15 kA
Nominal tightening torque down terminal	3.60 - 3.60 Nm
Nominal tightening torque top terminal	3.60 - 3.60 Nm

**Power**

Total power loss under I <sub>N</sub>	6.48 W
---------------------------------------	--------

**Endurance**

Electric endurance in number of cycles	4,000
Number of mechanical operations	20,000

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 70 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 50 mm <sup>2</sup>

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Air humidity protection	For all climates

**Capacity**

Number of modules	1.50
-------------------	------

**Connectivity**

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	90 mm
Width	27 mm
Depth	70 mm