



HMD190



### MCB 1P 15kA D-100A 1.5M

# **Technical properties**

Arc	hi	+~	-	IIFO

Type of pole	1P
Curve	D

## Voltage

Rated operational voltage Ue	240 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6,000 V

## Frequency

Frequency	50 - 60 Hz
-----------	------------

## Installation, mounting

Nominal tightening torque	3.5 - 5.0 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular	
devices	Screw terminal

### **Electric current**

Rated current	100 A
Rated service breaking capacity Ics AC according to IEC 60898-1	7.50 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	15 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	15 kA
Rated current at 0°C	124 A
Rated current 5°C	120 A
Rated current 10°C	116 A
Rated current 15°C	112 A
Rated current at 20°C	108 A
Rated current 25°C	104 A
Rated current 30°C	100 A
Rated current 35°C	96.60 A
Rated current at 40°C	93.10 A
Rated current at 45°C	89.40 A
Rated current at 50°C	85.60 A
Rated current 55°C	81.60 A
Rated current 60°C	77.50 A

Main electrical attributes	
Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	15 kA
Nominal tightening torque down terminal	3.60 - 3.60 Nm
Nominal tightening torque top terminal	3.60 - 3.60 Nm
Power	
Total power loss under IN	6.48 W
Endurance	
Electric endurance in number of cycles	4,000
Number of mechanical operations	20,000
Connection	
Cross-section of input and output with screws, for massive conductors	1 - 70 mm²
Cross-section of input and output with screws, for flexible conductors	1 - 50 mm²
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Air humidity protection	For all climates
Capacity	
Number of modules	1.50
Connectivity	
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Dimensions	
Height	90 mm
Width	27 mm
Depth	70 mm