



HIM406

## Modular change-over switch 3P+N 63A

### Technical properties

#### Voltage

Rated operational voltage U <sub>e</sub>	380 - 415 V
Rated insulation voltage U <sub>i</sub>	800 V
Rated impulse withstand voltage U <sub>imp</sub>	8,000 V

#### Electric current

Rated current	63 A
Rated short-time withstand current I <sub>cw</sub> IEC 60947	1.50 kA
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	50 kA

#### Power

Rated operational power under 400 V AC AC1	41,000 W
Total power loss under I <sub>N</sub>	6 W

#### Architecture

Number of poles	4
Control/operation element	Short rotary handle
Type of pole	3P+N

#### Dimensions

Height	76 mm
Width	140 mm
Depth	89 mm

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Cover, door

Interlockable	Yes
---------------	-----

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Capacity

Number of modules	8
-------------------	---

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	2.5 - 35 mm <sup>2</sup>
Cross-section rigid conductor	2.5 - 35 mm <sup>2</sup>