



HNB250H

Moulded Case Circuit Breaker X250 3P 40kA 250A TM

Technical properties

Electric current

Rated current	250 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated current 0°C according to IEC 60947	298.20 A
Rated current 10°C according to IEC 60947	287.20 A
Rated current 15°C according to IEC 60947	281.20 A
Rated current 20°C according to IEC 60947	275.20 A
Rated current 25°C according to IEC 60947	269.20 A
Rated current 30°C according to IEC 60947	263 A
Rated current at 35°C according to IEC 60947	256.50 A
Rated current at 40°C according to IEC 60947	250 A
Rated current 45°C according to IEC 60947	243.20 A
Rated current 50°C according to IEC 60947	236.20 A
Rated current 55°C according to IEC 60947	229.20 A
Rated current 5°C according to IEC 60947	292.70 A
Rated current at 60°C according to IEC 60947	222.20 A
Rated current 65°C according to IEC 60947	215 A
Rated current 70°C according to IEC 60947	207.50 A

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8,000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 415 V

Functions

Trip unit	TM A/A
Power	
Total power loss under IN	48 W
Endurance	
Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000
Safety	
Ingress Protection (IP) class	IP4X
Connection	
Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²
Settings	
Thermal protection knob setting xIN	0.63, 0.8, 1
Adjustment range short-term delayed short-circuit release	0 - 0 A
Cable	
Cable material	Copper
Compatibility	
Suitable for DIN Rail	No
Suitable for distribution board	Yes
Installation, mounting	
Mounting-/Connection Position	Front
Nominal tightening torque	12 - 12 Nm
Nominal tightening torque down terminal	12 - 12 Nm
Nominal tightening torque top terminal	12 - 12 Nm
Main electrical attributes	
Magnetic protection trip time	0 - 0 ms