




MCN302



## MCB 3P 6kA C-2A 3M

### Technical properties

#### Electric current

Rated current	2 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	10 kA
Rated current -15°C	2.5 A
Rated current -10°C	2.5 A
Rated current -5°C	2.4 A
Rated current at 0°C	2.4 A
Rated current 5°C	2.3 A
Rated current 10°C	2.2 A
Rated current 15°C	2.2 A
Rated current at 20°C	2.1 A
Rated current 25°C	2.1 A
Rated current 30°C	2 A
Rated current 35°C	1.9 A
Rated current at 40°C	1.9 A
Rated current at 45°C	1.8 A
Rated current at 50°C	1.7 A
Rated current 55°C	1.6 A
Rated current 60°C	1.5 A
Rated current 65°C	1.4 A
Rated current 70°C	1.4 A

#### Architecture

Type of pole	3P
Curve	C

#### Capacity

Number of modules	3
-------------------	---

#### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

#### Voltage

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	4.10 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	52.50 mm
Depth	70 mm