



NDN300A

## MCB 3P 10kA/15kA D-0.5A 3M

### Technical properties

#### Electric current

Rated current	0.50 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	15 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	30 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	15 kA
Rated current -25°C	0.69 A
Rated current at -20°C	0.67 A
Rated current -15°C	0.66 A
Rated current -10°C	0.64 A
Rated current -5°C	0.63 A
Rated current at 0°C	0.61 A
Rated current 5°C	0.59 A
Rated current 10°C	0.58 A
Rated current 15°C	0.56 A
Rated current at 20°C	0.54 A
Rated current 25°C	0.52 A
Rated current 30°C	0.50 A
Rated current 35°C	0.48 A
Rated current at 40°C	0.45 A
Rated current at 45°C	0.43 A
Rated current at 50°C	0.40 A
Rated current 55°C	0.37 A
Rated current 60°C	0.34 A
Rated current 65°C	0.31 A
Rated current 70°C	0.27 A

#### Architecture

Type of pole	3P
Curve	D

#### Capacity

Number of modules	3
-------------------	---

#### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
--	----------------

Nominal tightening torque down terminal	2.80 - 2.80 Nm
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

#### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	10 kA
---	-------

#### Voltage

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	6,000 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for massive conductors	1 - 35 mm²

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 - 70 °C

#### Power

Total power loss under I <sub>N</sub>	4.35 W
---------------------------------------	--------

#### Endurance

Electric endurance in number of cycles	4,000
Number of mechanical operations	20,000

#### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

#### Dimensions

Height	83 mm
--------	-------

Width	52.50 mm
Depth	70 mm