



SBN233

## 2-pole, 32A Modular Switch with big terminals

### Technical properties

#### Architecture

Number of poles	2
Neutral position	Without neutral
Type of pole	2P

#### Electric current

Rated current	32 A
Breaking capacity 400 V AC23A	677 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	0.48 kA
Acceptable current rating AC21 category A	32 A
Acceptable current rating AC21 category B	32 A
Acceptable current rating AC22 category A	32 A
Acceptable current rating AC22 category B	32 A
Rated short-circuit making capacity I <sub>cm</sub> under 240 V AC according to IEC 60947-3	0.67 kA
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	0.48 kA

#### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	Screw terminal

#### Voltage

Rated operational voltage U <sub>e</sub>	230 - 230 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	440 V
Rated impulse withstand voltage U <sub>imp</sub>	6,000 V

#### Capacity

Number of modules	2
-------------------	---

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Dimensions

Height	83 mm
Width	35 mm

Depth	68 mm
<b>Equipment</b>	
Number of NO contacts	2
Number of NC contacts	0
<b>Use conditions</b>	
Operating temperature	-20 - 70 °C
Storage/transport temperature	-40 - 80 °C
<b>Connection</b>	
Cross-section flexible conductor	2 - 16 mm <sup>2</sup>
Cross-section rigid conductor	2.5 - 25 mm <sup>2</sup>
<b>Endurance</b>	
Number of mechanical operations	60,000
Electrical durability at nominal load in AC21 in operating cycles	5,000
Electrical durability at nominal load in AC22 in operating cycles	5,000
<b>Power</b>	
Total power loss under IN	2.30 W
Power loss per pole at In	1.20 W
<b>Connectivity</b>	
Down connection alignment for modular devices	Shifted terminal
Top connection alignment for modular devices	Aligned terminal