



SBN363

3-pole, 63A Modular Switch

Technical properties

Architecture

Number of poles	3
Neutral position	Without neutral
Type of pole	3P

Electric current

Rated current	63 A
Breaking capacity 400 V AC23A	1,332 A
Rated conditional short-circuit current I _{cc} with gl-gG fuses	0.94 kA
Acceptable current rating AC21 category A	63 A
Acceptable current rating AC21 category B	63 A
Acceptable current rating AC22 category A	63 A
Acceptable current rating AC22 category B	63 A
Rated short-circuit making capacity I _{cm} under 415 V AC according to IEC 60947-3	1.33 kA
Rated short-time withstand current I _{cw} 1s IEC 60947	0.94 kA

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
---------------------------	----------------

Voltage

Rated operational voltage U _e	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U _i	440 V
Rated impulse withstand voltage U _{imp}	6,000 V

Capacity

Number of modules	3
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Height	83 mm
Width	52.50 mm
Depth	68 mm

Equipment

Number of NO contacts	3
Number of NC contacts	0

Use conditions

Operating temperature	-20 - 70 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor	2.5 - 16 mm ²
Cross-section rigid conductor	2.5 - 25 mm ²

Endurance

Number of mechanical operations	60,000
Electrical durability at nominal load in AC21 in operating cycles	5,000
Electrical durability at nominal load in AC22 in operating cycles	5,000

Power

Total power loss under IN	6.90 W
Power loss per pole at In	2.30 W

Connectivity

Top connection alignment for modular devices	Aligned terminal
---	------------------
