



WMGKSB/EL



## 20A Double Pole Key Switch Marked 'EM LTG TEST' Black

### Technical properties

#### Electric current

Momentary contact current	10 A
---------------------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Architecture

Number of poles	2
-----------------	---

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Controls and indicators

Number of buttons	0
With feedback signal contact	No

#### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Transparent	No

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Dimensions

Depth	24 mm
-------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Texts

Imprint	With imprint
Lighting	Without neon lamp
Related Systems	Hager sollysta