



16406094

Relay switch w. centre plate f. hotel card Q.x alu velvety. lacquered

Technical properties

Architecture

Number of keys 0

Configuration

Switch mode 1pole

Antibacterial treatment No

Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$ max. 6 A

Dimensions

Depth 57.3 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

LED control

LED illuminated with blue LED if hotel card is not inserted

Incandescent bulbs control

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Screw terminals (max.)	2 x 2,5 mm ²
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

Equipment

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

Use cases

Application	Light control ; Hotel application
-------------	-----------------------------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---