



SFT132

## 1-pole, 32A Centre Off Modular Changeover Switch with Top Common Point

### Technical properties

#### Architecture

Number of poles	1
Neutral position	Without neutral
Type of pole	1P

#### Electric current

Rated current	32 A
Breaking capacity 400 V AC23A	677 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	0.48 kA
Acceptable current rating AC21 category A	32 A
Acceptable current rating AC21 category B	32 A
Acceptable current rating AC22 category A	32 A
Acceptable current rating AC22 category B	32 A
Rated short-circuit making capacity I <sub>cm</sub> under 240 V AC according to IEC 60947-3	0.48 kA
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	0.48 kA

#### Installation, mounting

Nominal tightening torque	1.80 - 1.80 Nm
Type of bottom connection for modular devices	Screw terminal

#### Voltage

Rated operational voltage U <sub>e</sub>	230 - 230 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	440 V
Rated impulse withstand voltage U <sub>imp</sub>	4,000 V

#### Capacity

Number of modules	1
-------------------	---

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Dimensions

Height	83 mm
Width	17.50 mm

Depth	70 mm
<b>Equipment</b>	
Number of NO contacts	0
Number of NC contacts	0
<b>Use conditions</b>	
Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 80 °C
<b>Connection</b>	
Cross-section flexible conductor	1.5 - 10 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 16 mm <sup>2</sup>
<b>Endurance</b>	
Number of mechanical operations	200,000
Electrical durability at nominal load in AC21 in operating cycles	25,000
Electrical durability at nominal load in AC22 in operating cycles	25,000
<b>Power</b>	
Total power loss under IN	1.50 W
Power loss per pole at In	1.50 W
<b>Connectivity</b>	
Down connection alignment for modular devices	Shifted terminal
Top connection alignment for modular devices	Shifted terminal