



289610

1-10 V push-button rot. potentiometer, NO contact, soft-lock, light control

Technical properties

Architecture

Type of control unit Push & rotative

Controls and indicators

Control for activation of pulse relays

Connectivity

Interface according to DIN EN 61347-2-3

Interface for controlling electronic ballasts and Tronic transformers with 1 - 10 V interface, 105 W

Main electrical features

Nominal voltage 240 V

Frequency 50/60 Hz

Electric current

Control current 50 mA

Momentary-contact current max. 2 A

Fuse

Fuse short-circuit and overload proof (fine-wire fuse) ; with spare fuse

Dimensions

Axis dimension Ø 4 mm

Connection

Type of connection with screw terminals

Equipment

Lighting e.g. for fluorescent lamps and LV halogen lamps

Switches / socket outlets with push-button, NO contact

Use

Differentiation characteristic 3 - Sales Soft-lock

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage Light control

Main design line Light control

Instructions

Information text

To ensure same illumination, use only electronic ballasts and fluorescent lamps from the same manufacturers. Possible to change fuse without removing cover.