



29511909

LED signal light, RGB, S.1/B.3/B.7, p. white, matt, plastic

Technical properties

Main electrical features

Rated voltage 230 V AC

Power

Power consumption at 195 ... 265 V~, 50/60 Hz - max. 2 W

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Settings

Setting Brightness modifiable via potentiometer

Equipment

Lighting Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button

Switches / socket outlets colour is switchable via an external switch

Use cases

Application Light control

temperatur

Ambient temperature -5...40 °C

Identification

Secondary design line(s) Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Special note text For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.