



29516089

**LED signal light, RGB, Q.1/Q.3, p. white velvety**

**Technical properties**

**Main electrical features**

Rated voltage 230 V AC

**Power**

Power consumption at 195 ... 265 V~, 50/60 Hz - max. 2 W

**Materials**

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Settings**

Setting Brightness modifiable via potentiometer

**Equipment**

Lighting Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button

Switches / socket outlets colour is switchable via an external switch

**Use cases**

Application Light control

**temperatur**

Ambient temperature -5...40 °C

**Identification**

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

**Instructions**

Special note text For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.