



303550

## Series switch for hollow-wall mounting, module inserts

### Technical properties

#### Architecture

Type of control unit	double rocker
Fixing mode	surface-mounting

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Configuration

Switch mode	series
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	41.6 mm
Height	71 mm
Width	71 mm

#### Materials

Material	Plastic/metal
Surface appearance	matt

#### Installation, mounting

Installation mode	without spreader claws, low installation depth, for screw fastening
-------------------	---

#### Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals
Type of connection	Quickconnect

**Equipment**

---

Lighting	for lighting and monitoring circuit
Heating switch	No

---

**Use cases**

---

Application	Light control
-------------	---------------

---

**Safety**

---

Protection index IP	IP20
---------------------	------

---

**Identification**

---

Application, usage	Light control
Main design line	Light control

---