



16406094

**Relay switch w. centre plate f. hotel card Q.x alu velvety. lacquered**

**Technical properties**

**Architecture**

Number of keys 0

**Configuration**

Switch mode 1pole

Antibacterial treatment No

**Main electrical features**

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

**Electric current**

Inductive load at  $\cos \varphi = 0.6$  max. 6 A

**Dimensions**

Depth 57.3 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

**Power**

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

**Materials**

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

**Fluorescent bulbs control**

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

**LED control**

LED illuminated with blue LED if hotel card is not inserted

**Incandescent bulbs control**

**Installation, mounting**

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

**Connection**

|                        |                         |
|------------------------|-------------------------|
| Screw terminals (max.) | 2 x 2,5 mm <sup>2</sup> |
|------------------------|-------------------------|

|                    |                              |
|--------------------|------------------------------|
| Type of connection | with screw-in lift terminals |
|--------------------|------------------------------|

**Settings**

|                                     |                 |
|-------------------------------------|-----------------|
| Delay time incrementally adjustable | 0, 15, 30, 60 s |
|-------------------------------------|-----------------|

|         |   |
|---------|---|
| Setting | with potentiometer for incremental adjustment of delay time |
|---------|---|

**Equipment**

|          |                  |
|----------|------------------|
| Lighting | for illumination |
|----------|------------------|

|                |                             |
|----------------|-----------------------------|
| Potential-free | with potential-free contact |
|----------------|-----------------------------|

**Use cases**

|             |                                   |
|-------------|-----------------------------------|
| Application | Light control ; Hotel application |
|-------------|-----------------------------------|

**Safety**

|               |    |
|---------------|----|
| REACH conform | No |
|---------------|----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

|              |    |
|--------------|----|
| Halogen free | No |
|--------------|----|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...50 °C |
|-----------------------|------------|

|                               |  |
|-------------------------------|--|
| Storage/transport temperature | -25...70 °C (storage at > 45°C reduces the service life) |
|-------------------------------|--|

**Identification**

|                    |               |
|--------------------|---------------|
| Application, usage | Light control |
|--------------------|---------------|

|                  |                        |
|------------------|------------------------|
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
|------------------|------------------------|

|                          |   |
|--------------------------|---|
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |
|--------------------------|---|