



16406096

**Relay switch centre plate for hotel card, Q.x, ant. velvety, lacq.**

**Technical properties**

**Architecture**

Number of keys 0

**Configuration**

Switch mode 1pole

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

**Electric current**

Inductive load at  $\cos \varphi = 0.6$  max. 6 A

Switching current 10 A /230 V AC1

**Dimensions**

Depth 57.3 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

**Power**

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

**Materials**

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

**Fluorescent bulbs control**

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

**LED control**

LED illuminated with blue LED if hotel card is not inserted

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps 1500 W

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Screw terminals (max.) 2 x 2,5 mm<sup>2</sup>

Type of connection with screw-in lift terminals

**Settings**

Delay time incrementally adjustable 0, 15, 30, 60 s

Setting with potentiometer for incremental adjustment of delay time

**Scope of delivery**

With lamp No

**Equipment**

Contact less No

Lighting for illumination

Potential-free with potential-free contact

**Use cases**

Application Light control ; Hotel application

**Safety**

REACH conform No

Halogen free No

**Use conditions**

Operating temperature -5...50 °C

Storage/transport temperature -25...70 °C (storage at > 45°C reduces the service life)

**Identification**

Application, usage Light control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9