



16406096

**Relay switch centre plate for hotel card, Q.x, ant. velvety, lacq.**

**Technical properties**

**Architecture**

Number of keys	0
----------------	---

**Configuration**

Switch mode	1pole
-------------	-------

Antibacterial treatment	No
-------------------------	----

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	230 V
-----------------	-------

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

**Electric current**

Inductive load at $\cos \varphi = 0.6$	max. 6 A
--	----------

Switching current	10 A /230 V AC1
-------------------	-----------------

**Dimensions**

Depth	57.3 mm
-------	---------

Insertion depth	32 mm
-----------------	-------

Card width	max. 55 mm
------------	------------

Card thickness	0.8...1.2 mm
----------------	--------------

Height	71 mm
--------	-------

Width	71 mm
-------	-------

**Power**

Conventional transformers	1500 VA
---------------------------	---------

Electronic transformers	1500 W
-------------------------	--------

Power consumption	< 0.2 W
-------------------	---------

**Materials**

Colour of design line	anthracite
-----------------------	------------

Material / workmanship	lacquered
------------------------	-----------

Surface appearance	velvety
--------------------	---------

**Fluorescent bulbs control**

Compact fluorescent lamps	500 W
---------------------------	-------

Fluorescent lamps in duo circuit	1500 W
----------------------------------	--------

**LED control**

LED illuminated with blue LED if hotel card is not inserted

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps 1500 W

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Screw terminals (max.) 2 x 2,5 mm<sup>2</sup>

Type of connection with screw-in lift terminals

**Settings**

Delay time incrementally adjustable 0, 15, 30, 60 s

Setting with potentiometer for incremental adjustment of delay time

**Scope of delivery**

With lamp No

**Equipment**

Contact less No

Lighting for illumination

Potential-free with potential-free contact

**Use cases**

Application Light control ; Hotel application

**Safety**

REACH conform No

Halogen free No

**Use conditions**

Operating temperature -5...50 °C

Storage/transport temperature -25...70 °C (storage at > 45°C reduces the service life)

**Identification**

Application, usage Light control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9