



16408992

## Relay switch centre plate for hotel card, S.1, white glossy

### Technical properties

#### Architecture

Number of keys	0
Fixing mode	flush-mounting

#### Configuration

Switch mode	1pole
Antibacterial treatment	No

#### Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

#### Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
Switching current	10 A /230 V AC1

#### Dimensions

Depth	57.3 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm
Height	71 mm
Width	71 mm

#### Power

Conventional transformers	1500 VA
Electronic transformers	1500 W

#### Materials

Colour of design line	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	Plastic/metal

#### Fluorescent bulbs control

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

#### LED control

Subject to technical modifications

LED

illuminated with blue LED if hotel card is not inserted

---

### Incandescent bulbs control

---

230 V incandescent lamps and halogen lamps

1500 W

---

### Installation, mounting

---

Installation mode

with spreader claws

---

### Connection

---

Screw terminals (max.)

2 x 2,5 mm<sup>2</sup>

Type of connection

with screw-in lift terminals

---

### Settings

---

Delay time incrementally adjustable

0, 15, 30, 60 s

Setting

with potentiometer for incremental adjustment of delay time

---

### Equipment

---

Lighting

for illumination

Potential-free

with potential-free contact

---

### Use cases

---

Application

Light control, Hotel application

---

### Safety

---

Protection index IP

IP20

---

### Use conditions

---

Operating temperature

-5...50 °C

Storage/transport temperature

-25...70 °C (storage at > 45°C reduces the service life)

---

### Identification

---

Application, usage

Light control

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1, Berker B.3, Berker B.7