



16409909

**Relay switch centre plate for hotel card, S.1/B.3/B.7, p. white, matt, plastic**

**Technical properties**

**Architecture**

Number of keys	0
Fixing mode	flush-mounting

**Configuration**

Switch mode	1pole
Antibacterial treatment	No

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

**Electric current**

Inductive load at $\cos \varphi = 0.6$	max. 6 A
Switching current	10 A /230 V AC1

**Dimensions**

Depth	57.3 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm
Height	71 mm
Width	71 mm

**Power**

Conventional transformers	1500 VA
Electronic transformers	1500 W

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal
Surface appearance	matt

**Fluorescent bulbs control**

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

---

**LED control**

LED	illuminated with blue LED if hotel card is not inserted
-----	---

---

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps	1500 W
--	--------

---

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

---

**Connection**

Screw terminals (max.)	2 x 2,5 mm <sup>2</sup>
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

---

**Settings**

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

---

**Equipment**

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

---

**Use cases**

Application	Light control, Hotel application
-------------	----------------------------------

---

**Safety**

Protection index IP	IP20
---------------------	------

---

**Use conditions**

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

---

**Identification**

Application, usage	Light control
--------------------	---------------

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------