



16417114

Relay switch centre plate for hotel card, K.5, stainless steel lacq.

Technical properties

Architecture

Fixing mode flush-mounting

Configuration

Switch mode 1pole

Antibacterial treatment No

Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$ max. 6 A

Switching current 10 A /230 V AC1

Dimensions

Depth 58.6 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Materials

Colour of design line stainless steel

Colour stainless steel

Colour stainless steel optics

RAL colour RAL 9022 - Pearl light grey

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

LED control

LED	illuminated with blue LED if hotel card is not inserted
-----	---

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	1500 W
--	--------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Screw terminals (max.)	2 x 2,5 mm ²
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

Equipment

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

Use cases

Application	Light control, Hotel application
-------------	----------------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Berker K.5
------------------	------------