



167504

## Neon lamp unit N terminal, light control, orange

### Technical properties

#### Controls and indicators

Rocker switch/rocker push-button	for rocker push-buttons and multiple rockers push-buttons, except order no. 503404, 503808, for change-over/intermediate switch and on/off switch, 2-pole, 10 AX
----------------------------------	--

#### Main electrical features

Rated current	0.4 mA
---------------	--------

#### Dimensions

Insertion depth	13 mm
-----------------	-------

#### Materials

Colour independent of design lines	orange
------------------------------------	--------

#### Equipment

Lighting	for lighting and monitoring circuit
Combination rocker switches/rocker push-buttons	for series switch illuminated

#### Use cases

Application	Light control
-------------	---------------

#### Identification

Application, usage	Light control
Main design line	Light control
Secondary design line(s)	Light control, ACCESSORIES

#### Instructions

Special note text	Refer to the overview for the matching flush-mounted inserts. ; these marked articles (see symbol) are only suitable for the water-protected flush-mounted installation IP44 in conjunction with the corresponding seal, frame and contact protection box (imprint "IP44").
-------------------	---

Information text	When several neon lamp units are used, the lamp current may result in malfunctioning of the relay/pulse relay. Remedy: Carry along a neutral conductor or connect a capacitor 230 V (1 $\mu$ F per 10 mA neon lamp current) in parallel with the coil.
------------------	--