



181113

Push-button, NO contact, TS, stainless steel matt, brushed nickel

Technical properties

Architecture

Type of control unit	Push button
----------------------	-------------

Configuration

Switch mode	Normally open contact
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	12 V
Rated voltage	12 V

Electric current

Momentary-contact current	1.5 A
---------------------------	-------

Dimensions

Depth	19.7 mm
Insertion depth	13 mm
Height	22 mm
Width	22 mm

Materials

Colour of design line	stainless steel
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	Nickel brushed
Material	nickel
Surface appearance	matt
Material / surface	brass, refined

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Scope of delivery

With lamp	No
-----------	----

Equipment	
Quantity of NC contacts	1
Quantity of NO contacts	1
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-20...60 °C
Identification	
Main design line	Berker TS
Instructions	
Special note text	For connection via system interfaces to radio bus, KNX radio or KNX installations. Alternatively, can be used to control relay circuits.