



3315436089

**High definition soc. out. 90° plug connection, Q.x, p. white velvety**

#### Technical properties

##### Architecture

|                 |        |
|-----------------|--------|
| Number of poles | 19pole |
|-----------------|--------|

##### Connectivity

|        |                      |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

|                    |   |
|--------------------|---|
| Connectors / jacks | with HDMI double socket, type A, supports HDMI technology (V 2.1) |
|--------------------|---|

##### Dimensions

|                 |       |
|-----------------|-------|
| Insertion depth | 41 mm |
|-----------------|-------|

##### Frequency

|                            |            |
|----------------------------|------------|
| Frequency range (vertical) | 50...85 Hz |
|----------------------------|------------|

##### Screen

|            |                     |
|------------|---------------------|
| Resolution | max. 1920 x 1080 px |
|------------|---------------------|

##### Storage

|                   |                  |
|-------------------|------------------|
| Transmission rate | max. 8.16 Gbit/s |
|-------------------|------------------|

##### Materials

|                       |             |
|-----------------------|-------------|
| Colour of design line | polar white |
|-----------------------|-------------|

|            |                       |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

|                    |         |
|--------------------|---------|
| Surface appearance | velvety |
|--------------------|---------|

|                    |                      |
|--------------------|----------------------|
| Material / surface | gold-plated contacts |
|--------------------|----------------------|

##### Installation, mounting

|                   |  |
|-------------------|--|
| Installation mode | without spreader claws ; for screw fastening |
|-------------------|--|

##### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

##### Identification

|                    |                          |
|--------------------|--------------------------|
| Application, usage | Communication technology |
|--------------------|--------------------------|

|                  |                        |
|------------------|------------------------|
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
|------------------|------------------------|

|                          |   |
|--------------------------|---|
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |
|--------------------------|---|

##### Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"  
for compliance with the permissible bending radii,  
Art. No. 1068-02 or 9062-74 ; For the connection of  
digital devices for transmission of high-resolution  
audio and video signals, such as satellite receivers  
and DVD players, to LCD or plasma screens. ;  
Observe the instructions of the cable and device  
manufacturers for maximum HDMI cable lengths! ;  
Fränkische: "Multimedia tube" for laying pre-  
assembled connection cable, Art. no. 294.10.092