



29516084

## LED signal light RGB Q.1/Q.3 alu velvety, lacquered

### Technical properties

#### Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

#### Power

Power consumption	at 195 ... 265 V~, 50/60 Hz - max. 2 W
-------------------	--

#### Materials

Colour of design line	aluminium
Material / workmanship	lacquered
Surface appearance	velvety

#### LED control

Quantity LED lamps	4
--------------------	---

#### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

#### Connection

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

#### Settings

Setting	Brightness modifiable via potentiometer
---------	---

#### Equipment

Lighting	Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
Switches / socket outlets	colour is switchable via an external switch

#### Use cases

Application	Light control
-------------	---------------

#### temperatur

Ambient temperature	-5...40 °C
---------------------	------------

#### Identification

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

#### Instructions

Special note text	For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.
-------------------	--