



382610

Change-over switch 2pole for lock cylinders, light control

Technical properties

Architecture

Type of control unit	Key
Fixing mode	surface-mounting

Configuration

Switch mode	2-pole off/change-over
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	16 AX (200 W Self Ballasted Lamp (SBL))
-------------------	-----------------------------------------

Dimensions

Depth	40.1 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---------------------------------------------

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
----------	------------------------------------------

Closures / Key systems	for master-key systems
Lock cylinder	for lock cylinder
Heating switch	No
Use cases	
Application	Blind control, Light control
Safety	
Protection index IP	IP20
Identification	
Application, usage	Light control
Main design line	Light control
Instructions	
Information text	for standardised profile half-cylinder lock, 40 mm