



29531606

## LED signal light, white lighting, B.3/B.7, ant., matt

### Technical properties

#### Main electrical features

Rated voltage 230 V AC

#### Power

Power consumption at 230 V~, 50 Hz - max. 1 W

#### Materials

Colour of design line anthracite

Surface appearance matt

#### LED control

Quantity LED lamps 4

#### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

#### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

#### Settings

Setting Brightness modifiable via potentiometer

#### Equipment

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

#### Use cases

Application Light control

#### Safety

REACH conform Yes

RoHS conform Yes

#### temperatur

Ambient temperature -5...40 °C

#### Identification

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1 ; Berker B.3 ; Berker B.7