



41086086

## Technical properties

### Architecture

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

### Controls and indicators

|         |                            |
|---------|----------------------------|
| Message | with acoustic fault signal |
|---------|----------------------------|

### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

### Voltage

|                        |   |
|------------------------|---|
| Overvoltage protection | according to EN 61643 and VDE 0675-6-11 |
|------------------------|---|

### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

### Dimensions

|                 |       |
|-----------------|-------|
| Insertion depth | 32 mm |
|-----------------|-------|

### Cover, door

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

### Materials

|                        |                          |
|------------------------|--------------------------|
| Colour of design line  | anthracite               |
| Colour                 | anthracite               |
| Colour                 | anthracite charcoal grey |
| RAL colour             | RAL 7021 - Black grey    |
| Material / workmanship | lacquered                |
| Material               | thermoplastic            |
| Surface appearance     | velvety                  |

### Installation, mounting

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

### Connection

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
|----------------------|--------------------------|

|   |  |
|---|--|
| Connection terminals                          | according to VDE 0620-1                                  |
| Type of connection                            | with screw terminals                                     |
| <b>Equipment</b>                              |  |
| Lighting                                      | with indicator LED for On/Error                          |
| <b>Use cases</b>                              |  |
| Application                                   | Security and safety systems                              |
| <b>Use</b>                                    |  |
| Differentiation characteristic 1 - Sales      | with labelling field                                     |
| Differentiation characteristic 3 - Sales      | Screw terminals  |
| <b>Safety</b>                                 |  |
| IK protection code against mechanical impacts | 05   |
| Protection index IP                           | IP20   |
| Protection                                    | without enhanced contact protection                      |
| With enhanced contact protection              | No   |
| <b>Identification</b>                         |  |
| Main design line                              | Berker Q.1/Q.3/Q.7/Q.9                                   |
| Secondary design line(s)                      | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9           |
| <b>Instructions</b>                           |  |
| Information text                              | Labelling field height arranged for P-touch strips 6 mm. |