



41096084

## SCHUKO socket outlet with LED orientation light, Q.x, alu velvety, lacquered

### Technical properties

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

#### Power

Power consumption 0.25 W/0.35 VA

#### Cover, door

Cover Central cover plate

#### Detection

Sensor integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness

#### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

#### Lighting control

Switch-off brightness 4 lx

Switch-on brightness 2 lx

Light intensity (white) 0.2 cd

#### LED control

LED white LED light ; long service life of the LED

#### Installation, mounting

**Connection**

Conductor cross-section (rigid)	max. 2.5 mm <sup>2</sup>
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

**Cable**

Wiring	through-wiring possible, therefore also ideal for retrofitting
--------	--

**Equipment**

Lighting	additional benefit by combination of a socket outlet with an orientation light
----------	--

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

**Instructions**

Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.
------------------	--