



29538989

## LED signal light, white lighting, S.1/B.3/B.7, p. white glossy

### Technical properties

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

#### Power

Power consumption	at 230 V~, 50 Hz - max. 1 W
-------------------	-----------------------------

#### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal

#### LED control

Quantity LED lamps	4
--------------------	---

#### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

#### Connection

Conductor cross-section	2.5 mm²
-------------------------	---------

#### Settings

Setting	Brightness modifiable via potentiometer
---------	---

#### Equipment

Lighting	Light colour cold white
Switches / socket outlets	switchable via separate switch

#### Use cases

Application	Light control
-------------	---------------

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification	
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7