



303212

## On/off switch 2pole 16 AX, light control

### Technical properties

#### Architecture

Type of control unit	single rocker
Fixing mode	surface-mounting

#### Configuration

Switch mode	2-pole off, with predefined neutral position
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

#### Electric current

Switching current	16 AX (200 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	42 mm
Insertion depth	32 mm
Height	71 mm
Width	71 mm

#### Materials

Material	Plastic/metal
Surface appearance	matt

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with screw terminals
Type of connection	Screw connection

---

**Equipment**

---

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

---

Heating switch	No
----------------	----

**Use cases**

---

Application	Light control
-------------	---------------

**Safety**

---

Protection index IP	IP20
---------------------	------

---

Impact strength	IK07
-----------------	------

**Identification**

---

Appliance switch type	No
-----------------------	----

---

Main design line	Light control
------------------	---------------

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.
------------------	--