



41101909

SCHUKO soc.out. LED,labfield,enhncd contact prot.,screw-in lift term.,S1/B3/7,wh

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 2 - Sales

enhanced contact protection

Differentiation characteristic 3 - Sales

with screw-in lift terminals

Safety

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1, Berker B.3, Berker B.7

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm.