



41102045

SCHUKO soc.out. control LED,enhncd contact prot.,screw-in lift term.,R.1.3,bl.

Technical properties

Architecture

| | |
|-------------|------------------------|
| Design | according to DIN 49440 |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|-----------------|-------|
| Insertion depth | 32 mm |
|-----------------|-------|

Cover, door

| | |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

Materials

| | |
|-----------------------|----------------------|
| Colour of labelling | 217,217,217 |
| Colour of design line | black |
| Colour | black |
| Colour | deep black |
| RAL colour | RAL 9005 - Jet black |
| Material | thermoplastic |
| Material for printing | PC-PMA black |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|------------------------------|
| Connection terminals | according to VDE 0620-1 |
| Type of connection | with screw-in lift terminals |

Settings

| | |
|-------------------|------------|
| Shading parameter | R1_czarny |
| Laser parameter | R1_schwarz |

Equipment

Type of configuration

Laserdruck

Use

Differentiation characteristic 1 - Sales

with labelling field

Differentiation characteristic 2 - Sales

enhanced contact protection

Differentiation characteristic 3 - Sales

Screw-in lift terminals

Safety

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

Identification

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1, Berker R.3, Berker R.8

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm.