



41107114

**SCHUKO soc.out. LED+ "ZSV" impr.,labfield,enhncd contact prot.,screw-in lift ,K1**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Design lines special colours	orange
Colour	orange
Colour	orange
RAL colour	RAL 2003 - Pastel orange
Material	thermoplastic

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

**Use**

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

**Standards**

Execution SV, ZSV

according to VDE 0100-710

**Safety**

IK protection code against mechanical impacts

05

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

**Identification**

Main design line

Berker K.1

**Instructions**

Information text

Labelling field height arranged for P-touch strips 6 mm. ; Insert colour-coded.