



395619

Pullcord push-button, change-over contact sep. signal contact, light control

Technical properties

Architecture

Type of control unit	pull cord
----------------------	-----------

Configuration

Switch mode	change-over contact, with separate signal contact
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	42 mm
Insertion depth	31.2 mm
Contact spacing	> 3 mm
Height	71 mm
Width	71 mm

Length

Long pullcord	14 cm
---------------	-------

Materials

Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	for wall and ceiling mounting, with spreader claws
-------------------	--

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Use cases

Application	Light control, Hospital application
-------------	-------------------------------------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Identification

Application, usage	Light control
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--