



41236089

**SCHUKO soc.out., enhncd contact prot., screw-in lift term., Q.x, p.wh.velv.**

#### Technical properties

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

Metallic colour No

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

##### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

<b>Safety</b>		
IK protection code against mechanical impacts		02
REACH conform		No
RoHS conform		Yes
Halogen free		Yes
Protection	Enhanced contact protection	
With enhanced contact protection		Yes
<b>Identification</b>		
Main design line	Berker Q.1/Q.3/Q.7/Q.9	
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9	