



41081404

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Controls and indicators

Message with acoustic fault signal

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Voltage

Overvoltage protection according to EN 61643 and VDE 0675-6-11

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

Equipment

Lighting with indicator LED for On/Error

Use cases

Application	Security and safety systems
-------------	-----------------------------

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 3 - Sales	Screw terminals
--	-----------------

Safety

IK protection code against mechanical impacts	05
---	----

Halogen free	No
--------------	----

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

Identification

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7
--------------------------	--------------------------------------

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--