



41081909

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

Equipment

Lighting	with indicator LED for On/Error
----------	---------------------------------

Use cases

Application	Security and safety systems
-------------	-----------------------------

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 3 - Sales	Screw terminals
--	-----------------

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP20
---------------------	------

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

Identification

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--