



41086089

## Technical properties

### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

### Configuration

Number of modules	1
-------------------	---

### Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

### Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

### Electric current

Rated current	16 A
---------------	------

### Dimensions

Insertion depth	32 mm
-----------------	-------

### Cover, door

Cover	Central cover plate
-------	---------------------

### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	velvety

### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

**Equipment**

Lighting	with indicator LED for On/Error
----------	---------------------------------

**Use cases**

Application	Security and safety systems
-------------	-----------------------------

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 3 - Sales	Screw terminals
--	-----------------

**Safety**

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP20
---------------------	------

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

**Identification**

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	--

**Instructions**

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--