



41431404

**SCHUKO soc. out., screw-in lift terminals, B.7, al., matt, lacq.**

### Technical properties

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

#### Use

Differentiation characteristic 3 - Sales Screw-in lift terminals

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

**Identification**

---

Main design line

Berker S.1/B.3/B.7

---

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7