



41088962

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	red
Colour	red
Colour	red
RAL colour	RAL 3003 - Ruby red
Material	thermoplastic

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals

Equipment

Lighting with indicator LED for On/Error

Use cases

Application Security and safety systems

Use

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 3 - Sales Screw terminals

Safety

IK protection code against mechanical impacts 05

Protection index IP IP20

Protection without enhanced contact protection

With enhanced contact protection No

Identification

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1, Berker B.3, Berker B.7

Instructions

Information text Labelling field height arranged for P-touch strips 6 mm.