



41088982

## Technical properties

### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

### Configuration

Number of modules	1
-------------------	---

### Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

### Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

### Electric current

Rated current	16 A
---------------	------

### Dimensions

Insertion depth	32 mm
-----------------	-------

### Cover, door

Cover	Central cover plate
-------	---------------------

### Materials

Colour of design line	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic

### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals

---

**Equipment**

Lighting with indicator LED for On/Error

---

**Use cases**

Application Security and safety systems

---

**Use**

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 3 - Sales Screw terminals

---

**Safety**

IK protection code against mechanical impacts 05

Protection index IP IP20

Protection without enhanced contact protection

With enhanced contact protection No

---

**Identification**

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1, Berker B.3, Berker B.7

---

**Instructions**

Information text Labelling field height arranged for P-touch strips 6 mm.