



41102089

SCHUKO soc.out. control LED, enhanced contact protection, screw-in lift terminal, R.1.3, white

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 105,105,105

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

Settings

Shading parameter R1_biały

Laser parameter R1_weiß

Equipment

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--