



41527104

SCHUKO socket outlet w. overvoltage protection, K.5, stainless steel, lacquered

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Controls and indicators

Message with acoustic fault signal

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Voltage

Overvoltage protection according to EN 61643 and VDE 0675-6-11

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line stainless steel

Material / workmanship lacquered

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

Equipment

Lighting with indicator LED for On/Error

Use cases

Application

Security and safety systems

Use

Differentiation characteristic 1 - Sales

with labelling field

Differentiation characteristic 3 - Sales

Screw terminals

Safety

IK protection code against mechanical impacts

07

Protection

without enhanced contact protection

With enhanced contact protection

No

Identification

Main design line

Berker K.5

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm.