



41527106

SCHUKO socket outlet with overvoltage protection, K.1, anthracite matt

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Controls and indicators

Message with acoustic fault signal

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Voltage

Overvoltage protection according to EN 61643 and VDE 0675-6-11

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

Equipment

Lighting with indicator LED for On/Error

Use cases

| | |
|-------------|-----------------------------|
| Application | Security and safety systems |
|-------------|-----------------------------|

Use

| | |
|--|----------------------|
| Differentiation characteristic 1 - Sales | with labelling field |
|--|----------------------|

| | |
|--|-----------------|
| Differentiation characteristic 3 - Sales | Screw terminals |
|--|-----------------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 07 |
|---|----|

| | |
|--------------|----|
| Halogen free | No |
|--------------|----|

| | |
|------------|-------------------------------------|
| Protection | without enhanced contact protection |
|------------|-------------------------------------|

| | |
|----------------------------------|----|
| With enhanced contact protection | No |
|----------------------------------|----|

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

Instructions

| | |
|------------------|--|
| Information text | Labelling field height arranged for P-touch strips 6 mm. |
|------------------|--|