



41527106

SCHUKO socket outlet with overvoltage protection, K.1, anthracite matt

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals

Equipment

Lighting	with indicator LED for On/Error
----------	---------------------------------

Use cases

Application	Security and safety systems
-------------	-----------------------------

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	Screw terminals

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--